

All Suggested Accessories sold seperately



- MB-1-4: HC 4 DX element
- MB-1-5: HC5 Rag chew element
- MB-1-6: HC 6 NEW full range element
- MB-1-iC: High performance condenser for iCOM radios

Microphone booms easily attach to the Heil Quiet Phone Pro and can be mounted for left or right side. Heil AD-1 adapters will be needed to interface your particular amateur radio transceiver.

All in and out of warranty items returned must be accompanied by a completed Heil hospital form, which can be found at www.heil-sound.com/amateur/heil_hospital.htm
Heil Sound, Ltd. warrants these products to the original purchaser for a period of one year parts and 90 days labor from the date of purchase. It does not cover accidental or intentional damage. Heil Sound, Ltd. is not responsible for loss, damage or expenses that arise from the use or the inability to use this product.

Heil Sound Ltd.
5800 North Illinois
Fairview Heights, IL 62208

(618) 257-3000 phone
(618) 257-3001 fax
info@heilsound.com

w w w . h e i l s o u n d . c o m



Quiet Phone™ Pro



Quiet Phone_{TM} Pro patent pending

Active noise canceling headset from Heil Sound, Ltd.

The Heil QUIET PHONE PRO is a result of years of research and development at Heil Sound, Ltd. While typical headsets are designed to reproduce audio, they pay no attention to the outside environment. In most cases, the ambient room noise is louder than the program information that comes through the speakers in the headphones.

Using the absolute latest active circuitry, Heil Sound has solved this problem. The ANC (active noise canceling) technology uses two small microphones placed deep inside each headphone speaker and wired to a differential amplifier, which switches the mics in or out of phase. As the microphones listen to the outside ambient noise as well as the high quality program information, the out-of-phase background noises are greatly reduced, particularly at frequencies below 400 Hz. So now you can enjoy your program source peacefully! Blower noise, jet engine noise, outside car traffic, ambient room noise, or the TV in the next room will all be reduced to levels tens of decibels below your program.

The most unique feature of this Heil Sound product is the optional Microphone Boom Assembly. Removing the small rubber plug, located above the ON/OFF switch, exposes a sturdy brass insert that allows attaching one of the five boom assemblies to the QUIET PHONE PRO. You can choose any of five different types of microphone elements that match various amateur radio transmitters, computers, podcasting and commercial radio/TV broadcasting. Your Heil QUIET PHONE PRO has now been turned into a very high quality professional boomset.

- Soft Replaceable Leatherette cushions with adjustable headband to ensure most comfortable listening for extended periods of time.
- Earphone speakers fold into headband for ease of packing.

Speaker type	Closed Dynamic
Drive unit size	High output 40 mm using Neodymium magnet assembly
Impedance	32Ω
Input Sensitivity	104 dB/mW
Frequency Response	20 - 20,000Hz
Cord Lengths	Comes with two detachable cables. Your choice of a 6' Heilwire straight cable or a 3' to 6' extendable coil cable.
Plug Type	Gold-plated stereo mini plug (0.5m), gold-plated L type stereo mini plug (1.5m); 1/8 inch to 1/4 inch adapter supplied.
Power	DC 1.5V - one AAA battery: 70 hours nominal battery life
ANC circuit	Active Noise reduction range: 40 Hz - 1 kHz
Weight	195g
Optional Accessories	Microphone boom attachment, Bag 2



To open battery cover depress tab at the bottom of the right ear cup.